

BDBLCS3K2

by Burndy
Catalog ID: BDBLCS3K2

Prop 65 Notice

POWER DISTRIBUTION BLOCKS.



Product Details

General

Insulation	Y
Material	Aluminum
Number Of Poles	2
Plated	Y
Plating Type	Tin
Temperature Rating	194° F
Trade Name	VERSIPOLE™
UPC	781810676073
UPC 12 Digit	7818106760733

Dimensions

Dimension - Height inch	4.15
Dimension - L Length Overall mm	157
Dimension - Length Overall inch	6.17

Electrical Ratings

Amperage Rating	310 A
Rating - Minimum Voltage	600
Voltage - Maximum	600 V

Conductor Related

Conductor - AL Str Run Range	6 AWG - 350 kcmil
Conductor - AL Str Tap Range	14 AWG - 2/0 AWG
Conductor - Copper Str Run Range	6 AWG - 350 kcmil
Conductor - Copper Str Tap Range	14 AWG - 2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • AL C Str-Tap • CU C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - cULus	Yes
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)