



BDBMCS2F3FS

by Burndy
Catalog ID: BDBMCS2F3FS

Prop 65 Notice

POWER DISTRIBUTION BLOCKS.

Product Details

General

| | |
|--------------------|---------------|
| Insulation | Y |
| Material | Aluminum |
| Plated | Y |
| Plating Type | Tin |
| Temperature Rating | 194 |
| Trade Name | VERSIPOLE™ |
| UPC | 781810676899 |
| UPC 12 Digit | 7818106768999 |

Dimensions

| | |
|--------|---------|
| Height | 4.52 in |
| Length | 5.71 in |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 600 V |

Conductor Related

| | |
|----------------|---|
| Conductor Type | <ul style="list-style-type: none">• AL C Str-Run• CU C Str-Run• AL C Str-Tap• CU C Str-Tap |
|----------------|---|

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - cULus | Yes |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)