

CT120800L

by Burndy
Catalog ID: CT120800L

Nylon cable Tie, 120 lbs, Installation Tool: TWT2, MK9, CTT50.

- Standard Cable Tie
Standard Cable Ties, Installation Tool: TWT2, MK9 Tool



Product Details

General

Application	For general purpose applications
Color	Natural
Color Code	Natural
Material	Nylon 6/6
Operating Temperature Celcius Max	85 °C
Operating Temperature Celcius Min	-40 °C
Rating - Minimum Tensile Strength N	120
Rating - Minimum Tensile Strength lbs	120
Sub Brand	UNIRAP
Tool Type	Standard
Trade Name	UNIRAP
Type	CT-L
UPC	781810661079
UPC 12 Digit	7818106610799

Dimensions

Dimension - Bundle Diameter Max inch	8
Dimension - L Length Overall mm	742 mm
Dimension - Length Overall inch	29.2 in
Dimension - Thread Size	-
Dimension - Width inch	0.30 in
Dimension - Width mm	8 mm

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	N
Certification - cULus	N
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	500 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)