



CT1751100QUG

by Burndy
Catalog ID: CT1751100QUG

Nylon cable ties, Tensile strength-175 Lbs, Color- UV Black, 36.00"L,
0.35"W, 11.00" Bundle Dia.

- Standard Cable Tie

Product Details

General

Color	Natural
Material	Nylon 6/6
Rating - Minimum Tensile Strength lbs	175
Tool Type	Heavy
Trade Name	UNIRAP™
UPC	781810486061

Dimensions

Dimension - Bundle Diameter Max inch	11
Dimension - L Length Overall mm	914 mm
Dimension - Length Overall inch	36.00 in
Dimension - Width inch	0.35 in
Dimension - Width mm	8.9 mm

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - UV Rated	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	500 EA
Minimum Pack Quantity	25

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)