



## GA25H29

by Burndy  
Catalog ID: GA25H29

Prop 65 Notice

Cast Cu Alloy Ground Clamp For H Beam, 2/0 Sol AWG - 250 Kcmil, 1-7/8 X 1-7/8 - 2-1/2X2-1/2 H-Beam

## Product Details

### General

Installation Torque Recommended Run in-lb	240 Lb in
Material	Copper
Plated	N
Plating Type	Unplated
UPC	781810001899
UPC 12 Digit	7818100018999

### Dimensions

Dimension - Height fraction	4-3/4 in
Dimension - Height inch	4.75 in
Dimension - Width inch	4 in
Dimension - Width mm	102 mm

### Conductor Related

Conductor - Copper Solid Size	2/0 AWG
Conductor - Copper Solid Size Range	2/0 Sol. - 250 kcmil
Conductor - Copper Str Size	250 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)