



## GK1129

by Burndy  
Catalog ID: GK1129

Prop 65 Notice

Cast Cu Alloy Grounding Clamp, 3 Cables to Rod or Pipe, 1/2" Rod Dia,  
1/4" IPS(A), 2/0 AWG Sol - 250 Kcmil Cu(AA)

## Product Details

### General

Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
Type	Three Cables to Rod or Tube
UPC	781810233689
UPC 12 Digit	7818102336899

### Dimensions

Dimension - B Length inch	1.63 in
Dimension - Height inch	2.50 in
Dimension - Width fraction	3-3/8 in
Dimension - Width inch	3.31 in
Dimension - Width mm	84 mm

### Conductor Related

Conductor - Copper Solid Size	2/0;3/0;4/0
Conductor - Copper Solid Size Range	2/0-4/0
Conductor - Copper Str Size	1/0;2/0;3/0;4/0;250
Conductor - Copper Str Size B Range	0.25
Conductor - Copper Str Size Range	1/0-250
Conductor - Copper Tube Std Size	0.5
Conductor - Copper Tube Std Size Range	0.5
Conductor - Rod Size	1/2 in
Conductor - Rod Size Range	1/2 in

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No

Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)