

TP106FBG25

by Burndy
Catalog ID: TP106FBG25

TERMINAL-POLYVINYLCHLORIDE INSULATED, FORK TONGUE.



Product Details

General

Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYDENT™
UPC	781810486375
UPC 12 Digit	7818104863755

Dimensions

Dimension - Length Overall inch	0.95 in
Dimension - Pad Width inch	0.28 in
Dimension - Stud Size inch	#4;#5
Dimension - Z inch	0.26 in

Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)