



## UCK2UL

by Burndy  
Catalog ID: UCK2UL

Prop 65 Notice

ACCOM: #6 AWG SOL/STR CU 1/4"- 5/16" GALV. STL GUY WIRE  
TORQUE: 110 in-lbs; DURIMUM™ Silicon Bronze Hardware; Tin-plated, copper

## Product Details

### General

Installation Torque Recommended in-lb	180 LBS/in
Material	Aluminum
Plated	Y
Plating Type	Tin - Electro Plated
UPC	781810120828
UPC 12 Digit	7818101208288

### Dimensions

Dimension - Height fraction	1-7/16 in
Dimension - Height inch	1.4375 in
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	1 in
Dimension - Width fraction	1-7/16 in
Dimension - Width inch	1.4375 in
Dimension - Width mm	37 mm

### Conductor Related

Conductor - Copper Solid Size B	6 Sol
Conductor - Copper Str Size B	6 Str
Conductor - Galvanized Steel Str Size Range	1/4 in -5/16 in

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)