



UCK3UL

by Burndy
Catalog ID: UCK3UL

Prop 65 Notice

ACCOM: #6-2 AWG SOL/STR CU BOTH GROOVES TORQUE: 110 in-lbs;
DURIUM™ Silicon Bronze Hardware; Tin-plated, copper

Product Details

General

Installation Torque Recommended in-lb	180 LBS/in
Material	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810120866
UPC 12 Digit	7818101208666

Dimensions

Dimension - Height fraction	1-7/16 in
Dimension - Height inch	1.4375 in
Dimension - L Length Overall mm	25 mm
Dimension - Length Overall inch	1 in
Dimension - Width fraction	1-7/16 in
Dimension - Width inch	1.4375 in
Dimension - Width mm	37 mm

Conductor Related

Conductor - Copper Solid Size A Range	6 Sol. - 2 Sol
Conductor - Copper Solid Size B Range	6 Str. - 2 Str
Conductor - Copper Str Size A	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size A Range	6 Str. - 2 Str
Conductor - Copper Str Size B	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Size B Range	6 Str. - 2 Str

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	20
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)