

# WCY57PB

by Burndy  
Catalog ID: WCY57PB

Prop 65 Notice

Wejtap Assembly, 336.4-600 kcmil (Run), 4-1 AWG (Tap), Wiring taps.

Features: With Yellow Power Booster, ANSI Class AA, Color Code: Yellow, Booster: WPBY Box 25, Conductor Size (tap - Mm): 7 - 8 SQ-MM, Installation Tool: WTRB Tool, Booster Color: Yellow, Conductor Type: Run: ACSR, AAC, Tap: ACSR, AAC, Copper, Cable Diameter Range (run): 0.666 - 0.893 IN, Conductor Size (run - Mm): 17 - 23 SQ-MM, Cable Diameter Range (tap): 0.257 - 0.326 IN



## Product Details

### General

|                |   |
|----------------|---|
| Application    | For use in tap applications using large run and tap conductor sizes |
| Color          | Yellow  |
| Connector Type | Tap   |
| Material       | Copper  |
| Sub Brand      | WEJTAP  |
| Trade Name     | WEJTAP™   |
| Type           | Wejtap Connector with Booster                                       |
| UPC            | 781810870518  |
| UPC 12 Digit   | 7818108705188   |

### Dimensions

|   |         |
|---|---------|
| Dimension - F Width Center to Center inch | 3 in    |
| Dimension - G inch                        | 1.53 in |

### Conductor Related

|                                |   |
|--------------------------------|---|
| Conductor - ACSR Str Run       | 300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole;397.5 (18/1) Chickadee;397.5 (24/7) Brant;397.5 (26/7) Ibis;397.5 (30/7) Larkspur;477.0 (18/1) Pelican;477.0 (24/7) Flicker;477.0 (26/7) Hawk;477.0 (30/7) Hen;556.5 (24/7) Parakeet |
| Conductor - ACSR Str Run Range | 300.0 (26/7) Ostrich-556.5 (24/7) Parakeet  |
| Conductor - ACSR Str Tap       | 4 (7/1) Swanate;3 (6/1) Swallow;2 (6/1) Sparrow;2 (7/1) Sparate;1 (6/1) Robin   |
| Conductor - ACSR Str Tap Range | 4 (7/1) Swanate-1 (6/1) Robin   |
| Conductor - AL Str Run         | 336.4;350;397.5;400;450;477;500;550;556.5;600   |
| Conductor - AL Str Run Range   | 336.4-600   |
| Conductor - AL Str Tap         | 4;3;2;1   |
| Conductor - AL Str Tap Range   | 4-1   |
| Conductor Type                 | <ul style="list-style-type: none"> <li>• ACSR C Str-Run</li> <li>• AL C Str-Run</li> <li>• ACSR C Str-Tap</li> <li>• AL C Str-Tap</li> </ul>  |

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Standards - RoHS Compliance Status | NC |

## Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)