



YA312N45

by Burndy
Catalog ID: YA312N45

Prop 65 Notice

Copper Two Hole HYLUG - Long Barrel ,45 Degree Pad 350 kcmil,1/2"
Bolt Hole with 1-3/4" Spacing,Tin Plated,Color: Red,Die Index: 18

Product Details

General

Color Code	Red
Connector Type	Terminal
Die Index	18;324
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810080238
UPC 12 Digit	7818100802388

Dimensions

Dimension - B Length fraction	2 in
Dimension - B Length inch	2.00 in
Dimension - Bolt Size fraction	1/2
Dimension - Height inch	2.54 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	135 mm
Dimension - Length Overall inch	5.31 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.88 in
Dimension - Pad Width inch	1.29 in
Dimension - Strip Length inch	2-1/16
Dimension - Z inch	0.64 in
Physical Attribute - Tongue Angle	45 Degree

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Navy Size	350 (91) Navy
Conductor - Copper Str Size	350 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	6
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)