

YA31TC58FXB

by Burndy
Catalog ID: YA31TC58FXB

Prop 65 Notice

Hylug; Belled; 5/8 IN Stud



Product Details

General

Color Code	White
Connector Type	Terminal
Die Index	17
Feature - Barrel Style	Belled
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810503720
UPC 12 Digit	7818105037200

Dimensions

Dimension - B Length fraction	2-3/16 in
Dimension - B Length inch	2.18 in
Dimension - Bolt Hole Size inch	0.69 in
Dimension - Bolt Size fraction	5/8
Dimension - Hole Size inch	0.69 in
Dimension - Hole Size mm	18 mm
Dimension - L Length Overall mm	105 mm
Dimension - Length Overall inch	4.15 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	0.88 in

Dimension - Pad Width inch	1.29 in
Dimension - Strip Length inch	2-1/4
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	262 (650/24) DLO
Conductor - Copper Flex I Size	250 kcmil
Conductor - Copper Flex K Size	250 kcmil
Conductor - Copper Flex M Size	250 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)