

YA34A3DT

by Burndy
Catalog ID: YA34A3DT

Prop 65 Notice

Aluminium Tube Hylug, 2 Holes w/o Inspection Window, Al-500 kcmil, Cu-500 kcmil, 600V-35kV, 1/2" stud, Closed, Compression, 0.56 in BCD, Pink



Product Details

General

Color Code	Pink
Connector Type	Terminal
Die Index	300
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
UPC	781810268384
UPC 12 Digit	7818102683844

Dimensions

Dimension - B Length fraction	2-5/16 in
Dimension - B Length inch	2.34 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.15 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	173 mm
Dimension - Length Overall inch	6.80 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	1.31 in
Dimension - Pad Width inch	1.62 in
Dimension - Strip Length inch	2 5/8
Dimension - Thread Size	1/2
Dimension - Z inch	0.77 in

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - AL Str Size	500 kcmil
Conductor - AL Str Size Range	500 kcmil
Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)