



YA34LNT12

by Burndy
Catalog ID: YA34LNT12

Prop 65 Notice

Copper Compression Lug, Narrow Tongue, 1 Hole w/ Inspection Window, 500 kcmil, 1/2" Stud, Short Barrel, Tin Plated.

UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available,Tongue Angle: Straight

Product Details

General

Application	For Code Conductor
Color Code	Brown
Connector Type	Terminal
Die Index	20
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	YA-L-NT
UPC	781810270219

Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.27 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	1.45 in
Dimension - L Length Overall mm	93 mm
Dimension - Length Overall inch	3.65 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	1.06 in
Dimension - Pad Width inch	0.96 in
Dimension - Strip Length inch	1-7/16
Dimension - Stud Size inch	1/2
Dimension - Z inch	0.92 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)