



YA4CL90

by Burndy
Catalog ID: YA4CL90

Prop 65 Notice

Cu Tubing HYLUG™, 1 Hole with Inspection Window, #4 AWG Code, 40 Navy, 600V-35kV, 1/4" stud, 8 or 346 index, Gray, 90 Degree Bend

Product Details

General

Color Code	Gray
Connector Type	Terminal
Die Index	8;346
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810019603

Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - D inch	0.58 in
Dimension - Height inch	1.22 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	21 mm
Dimension - Length Overall inch	0.84 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.34 in
Dimension - Pad Width inch	0.50 in
Dimension - Strip Length inch	7/8
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.33 in
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Navy Size	40 (19) Navy
Conductor - Copper Str Navy Size Range	40 (19) Navy
Conductor - Copper Str Size	4 AWG
Conductor - Copper Str Size Range	4 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)