

# YAE10N111LFBOX

by Burndy  
Catalog ID: YAE10N111LFBOX

Snap Fork Tongue, 12 AWG - 10 AWG, 4-6, 1.02 in L.

Features: Locking Fork Tongue, Rapid easy installation of terminal without complete removal of screw



## Product Details

### General

Application	Power Connector
Connector Type	Terminal
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Unplated
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	Long Barrel
UPC	781810524435
UPC 12 Digit	7818105244355

### Dimensions

Dimension - L Length Overall mm	26 mm
Dimension - Length Overall inch	1.02 in
Dimension - Pad Width inch	0.33 in
Dimension - Strip Length inch	11/32
Dimension - Stud Size fraction	#6;#8
Dimension - Stud Size inch	#6 - #8
Dimension - Z inch	0.29 in

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	1

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)