

# YAE10N112LFBOX

by Burndy  
Catalog ID: YAE10N112LFBOX

Cu Terminal, Snap Fork Tongue, 10-12 AWG, 300 V, #8-10 Stud, 1.02" L, 0.35" W, 3 PC Nylon Insul, Tin Plated, Yellow(Insul Color).

Features: Locking Fork Tongue, Rapid easy installation of terminal without complete removal of screw



## Product Details

### General

Application	For Easy Terminal Insertion And Removal
Connector Type	Terminal
Insulation	Y
Insulation Type	3 PC Nylon
Material	Copper
Physical Attribute - Tongue Type	Snap Fork
Plated	Y
Plating Type	Tin
Sub Brand	INSULUG
Trade Name	INSULUG™
Type	Long Barrel
UPC	781810524459
UPC 12 Digit	7818105244599

### Dimensions

Dimension - L Length Overall mm	26 mm
Dimension - Length Overall inch	1.02 in
Dimension - Pad Width inch	0.35 in
Dimension - Strip Length inch	11/32
Dimension - Stud Size fraction	#8;#9;#10
Dimension - Z inch	0.29 in

### Conductor Related

Conductor Range	#12 AWG to #10 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	1

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)