



YAE10N80FBOX

by Burndy
Catalog ID: YAE10N80FBOX

Fork Tongue Terminals, 12 AWG - 10 AWG, 4-6, 1.02 in L, .35 in W.

Package: Box

Product Details

General

Application	Power Connector
Color Code	Yellow
Connector Type	Fork Terminal
Feature - Barrel Type	Standard
Insulation	Y
Insulation Type	Nylon
Material	Copper
Physical Attribute - Tongue Type	Fork Terminal
Plated	Y
Plating Type	Electro Tin
Sub Brand	INSULUG
Temperature Rating	105° C
Trade Name	INSULUG™
Type	YAE-N
UPC	781810524473
UPC 12 Digit	7818105244733

Dimensions

Dimension - L Length Overall mm	26 mm
Dimension - Length Overall inch	1.02 in
Dimension - Pad Width inch	0.35 in
Dimension - Strip Length inch	3/8 in
Dimension - Stud Size inch	#4 - #6
Dimension - Z inch	0.29 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)