

YAG26LTC14FX

by Burndy
Catalog ID: YAG26LTC14FX

Prop 65 Notice

Cu Compression terminal



Product Details

General

| | |
|--------------------------------------|-----------------------------|
| Color Code | Black |
| Connector Type | Terminal |
| Die Index | 13 |
| Feature - Barrel Style | Chamfered |
| Feature - Barrel Type | Standard |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Plated | Y |
| Plating Type | Tin Plated |
| Temperature Rating | 194 |
| Trade Name | HYLUG™ |
| Type | Standard Barrel, Tin Plated |
| UPC | 781810100462 |
| UPC 12 Digit | 7818101004622 |

Dimensions

| | |
|-----------------------------------|---------|
| Dimension - B Length inch | 0.81 in |
| Dimension - Bolt Hole Size inch | 0.27 in |
| Dimension - Bolt Size fraction | 1/4 |
| Dimension - D inch | 0.64 in |
| Dimension - Hole Size inch | 0.27 in |
| Dimension - Hole Size mm | 7 mm |
| Dimension - L Length Overall mm | 50 mm |
| Dimension - Length Overall inch | 1.95 in |
| Dimension - N inch | 0.31 in |
| Dimension - Outside Diameter inch | 0.63 in |
| Dimension - Pad Width inch | 0.93 in |
| Dimension - Strip Length inch | 13/16 |
| Dimension - Stud Size inch | 1/4 |
| Dimension - Z inch | 0.33 in |

| | |
|-----------------------------------|----------|
| Physical Attribute - Tongue Angle | Straight |
|-----------------------------------|----------|

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|--|---|
| Conductor - Copper DLO Size | 2/0 (375/#24) DLO |
| Conductor - Copper Flex G Size | 2/0 AWG |
| Conductor - Copper Flex H Size | 2/0 AWG |
| Conductor - Copper Flex I Size | 2/0 AWG |
| Conductor - Copper Flex K Size | 2/0 AWG |
| Conductor - Copper Flex M Size | 2/0 AWG |
| Conductor - Copper Flex M Size Range | 2/0 AWG |
| Conductor - Copper Str Navy Size | 125 (61) Navy |
| Conductor - Copper Str Navy Size Range | 125 (61) Navy |
| Conductor - Copper Str Size | 2/0 AWG |
| Conductor - Copper Str Size Range | 2/0 AWG |
| Conductor - CopperWeld Str Size | 2/0 F AWG;2/0 G AWG;2/0 J AWG;2/0 K AWG;2/0 V AWG |
| Conductor - CopperWeld Str Size Range | 2/0 F AWG-2/0 V AWG |
| Conductor - Material | Copper |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)