

YAG27L2NTCFX

by Burndy
Catalog ID: YAG27L2NTCFX

Prop 65 Notice

Cu Tubing Hylug, 2 Holes w/o Inspection Window, 3/0 AWG Flex, 150 Navy, 600V-35kV, 1/2" stud, Standard, Compression, 0.56 in BCD, Orange.

Features: Compression Lug, Die Index:14, Strip Length: 1 IN



Product Details

General

Application	For Flex Conductor
Color Code	Orange
Connector Type	Terminal
Die Index	14
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin Plated
Sub Brand	TERMINALS, HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810100479
UPC 12 Digit	7818101004799

Dimensions

Dimension - B Length inch	1.00 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - D inch	3.03 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm

Dimension - L Length Overall mm	116 mm
Dimension - Length Overall inch	4.56 in
Dimension - N inch	0.63 in
Dimension - Outside Diameter inch	0.70 in
Dimension - Pad Width inch	1.03 in
Dimension - Strip Length inch	1 in
Dimension - Z inch	0.65 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	3/0 (450/#24) DLO
Conductor - Copper Flex G Size	3/0 AWG
Conductor - Copper Flex H Size	3/0 AWG
Conductor - Copper Flex I Size	3/0 AWG
Conductor - Copper Flex K Size	3/0 AWG
Conductor - Copper Flex M Size	3/0 AWG
Conductor - Copper Flex M Size Range	3/0 AWG
Conductor - Copper Str Navy Size	150 (61) Navy
Conductor - Copper Str Navy Size Range	150 (61) Navy
Conductor - Copper Str Size	3/0 AWG
Conductor - Copper Str Size Range	3/0 AWG
Conductor - CopperWeld Str Size	3/0 E AWG;3/0 EK AWG;3/0 F AWG;3/0 G AWG;3/0 J AWG;3/0 V AWG
Conductor - CopperWeld Str Size Range	3/0 E AWG-3/0 V AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)