



YAG28L2TC38FXTZ

by Burndy
Catalog ID: YAG28L2TC38FXTZ

Uninsulated Copper Compression Terminal, Tin-Zinc Plated, UL Listed 90° C, Up to 35 kV, 2 Hole

- No inspection window is ideal for more corrosive environments as the barrel transition is not open
- Barrel is designed with an internal chamfer at the wire entry to ensure smooth insertion of the wire, preventing possible damaging of the wire strands during insertion
- 45° and 90° angular lugs are available
- please contact Customer Service
- Tin-Zinc plated for battery connectors or other heavy duty equipment, reduce the corrosion from lead/acid batteries
- Connectors are clearly marked with stamping and barrel color coding
- Connectors accommodate both Flex and Code Wire

Product Details

General

| | |
|-------------|---|
| Application | <ul style="list-style-type: none"> • The use of Tin-Zinc is becoming more prevalent • we are seeing this used in appliances, aerospace, automotive, electrical connectors, marine equipment, mining, and other industries |
| Die Index | 15 |
| Material | Copper |
| Type | Cable to Flat |
| UPC | 621945555877 |

Dimensions

| | |
|-------------------------------|-----------|
| Dimension - B Length inch | 1.03 in |
| Dimension - Pad Width inch | 1.14 in |
| Dimension - Strip Length inch | 1-1/16 in |
| Dimension - Stud Size inch | 3/8 in |
| Length | 3.46 in |
| Thickness | 0.15 in |

Conductor Related

| | |
|--------------------------------|------------------|
| Conductor - Copper DLO Size | 4/0 (550/24) DLO |
| Conductor - Copper Flex G Size | 4/0 AWG |
| Conductor - Copper Flex H Size | 4/0 AWG |
| Conductor - Copper Flex I Size | 4/0 AWG |
| Conductor - Copper Flex K Size | 4/0 AWG |
| Conductor - Copper Flex M Size | 4/0 AWG |
| Conductor - Copper Str Size | 4/0 AWG |

Certifications and Compliance

| | |
|------------------------------|-----|
| Certification - CSA Approved | Yes |
|------------------------------|-----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)