

YAV1202M12

by Burndy
Catalog ID: YAV1202M12

Non Insul Cu Comp Tubular Terminal, Metric, 2 Hole/W/InspWindow, 120 mm, M12 Stud, Tin - Electro Plated, 15 Index



Product Details

General

Connector Type	Terminal
Die Index	15
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810442708
UPC 12 Digit	7818104427088

Dimensions

Dimension - B Length inch	26.2 in
Dimension - L Length Overall mm	113 mm
Dimension - Length Overall inch	4.43 in
Dimension - Pad Width inch	29.0 in
Dimension - Strip Length inch	1.06 in
Dimension - Z inch	0.55 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Str Size	4/0
Conductor - Copper Str Size Range	4/0
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)