

YAV120M16

by Burndy
Catalog ID: YAV120M16

Non Insulated Cu Tubular Terminal, 1 Hole, W/Insp Window, 120 mm, 16 mm Stud, 2.92 IN L, Compression, 15 Index, 27 mm Strip Length



Product Details

General

Connector Type	Terminal
Die Index	15
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810321997
UPC 12 Digit	7818103219977

Dimensions

Dimension - B Length fraction	1-1/8 in
Dimension - B Length inch	0.03 in
Dimension - D inch	1.24 in
Dimension - Hole Size inch	0.67 in
Dimension - Hole Size mm	17 mm
Dimension - Inside Diameter inch	0.59 in
Dimension - L Length Overall mm	4 mm
Dimension - Length Overall inch	0.15 in
Dimension - N inch	0.55 in
Dimension - Outside Diameter inch	0.75 in
Dimension - Pad Width inch	0.14 in
Dimension - Strip Length inch	1.06 in
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
-----------------------------------	-----

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)