

YAV150M16

by Burndy
Catalog ID: YAV150M16

Copper Compression Lug, Ring Tongue, 1 Hole w/ Inspection Hole, 150 mm, #16 Stud, Short Barrel, Tin Plated



Product Details

General

Connector Type	Terminal
Die Index	17
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810322093
UPC 12 Digit	7818103220933

Dimensions

Dimension - B Length inch	1.03 in
Dimension - Hole Size inch	0.69 in
Dimension - Hole Size mm	17.5 mm
Dimension - L Length Overall mm	74.7 mm
Dimension - Length Overall inch	2.94 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	0.81 in
Dimension - Pad Width inch	1.2 in
Dimension - Strip Length inch	1.06 in
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)