

YAV1852M16

by Burndy
Catalog ID: YAV1852M16

Non Insulated Cu Tubular Terminal, 2 Hole, W/Insp Window, 185 mm, 16 mm Stud, 4.76 IN L, Compression, 18 Index, 29 mm Strip Length



Product Details

General

Connector Type	Terminal
Die Index	18
Material	Copper
Plated	YES
Plating Type	Tin
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810442753
UPC 12 Digit	7818104427533

Dimensions

Dimension - B Length inch	1.06 in
Dimension - Hole Size inch	0.69 in
Dimension - Hole Size mm	17.5 mm
Dimension - L Length Overall mm	120.9 mm
Dimension - Length Overall inch	4.76 in
Dimension - Pad Width inch	32.8 in
Dimension - Strip Length inch	1.14 in
Dimension - Z inch	0.67 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
-----------------------------------	-----

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)