

YAV185FM16

by Burndy
Catalog ID: YAV185FM16

Non Insulated Cu Tubular Terminal, 1 Hole, W/Insp Window, 185 mm, M16 Stud, 3.18 IN L, Compression, 18 Index, 29 mm Strip Length



Product Details

General

Connector Type	Terminal
Die Index	18
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Yes
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810322147
UPC 12 Digit	7818103221477

Dimensions

Dimension - B Length inch	1.19 in
Dimension - Hole Size inch	0.69 in
Dimension - Hole Size mm	17.5 mm
Dimension - L Length Overall mm	81 mm
Dimension - Length Overall inch	3.18 in
Dimension - N inch	0.66 in
Dimension - Outside Diameter inch	0.95 in
Dimension - Pad Width inch	1.40 in
Dimension - Strip Length inch	1.14 in
Dimension - Z inch	0.67 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)