



YAV25RS4

by Burndy
Catalog ID: YAV25RS4

Copper Compression Right Angled Lug, Heavy Duty Right Angle Terminal, 1 Hole W/ Inspection Hole, AN-1/0 Flex, 5/8" Stud, Short Barrel, Tin Plated

Product Details

General

Connector Type	Terminal
Die Index	43
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Ring Tongue
UPC	621945149953

Dimensions

Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.69 in
Dimension - Bolt Hole Size inch	0.66 in
Dimension - G inch	1.49 in
Dimension - Hole Size fraction	2/3
Dimension - Hole Size mm	17 mm
Dimension - L Length Overall mm	37 mm
Dimension - Length Overall inch	1.46 in
Dimension - N inch	0.5 in
Dimension - Outside Diameter inch	0.58 in
Dimension - Pad Width inch	0.92 in
Dimension - Stud Size inch	5/8
Dimension - Z inch	0.63 in
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper Str Aircraft Size	AN 0
Conductor - Copper Str Aircraft Size Range	AN 0
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)