



YAV28RS12

by Burndy
Catalog ID: YAV28RS12

Copper Compression Right Angled Lug, Heavy Duty, 1 Hole W/ Inspection Hole, AN-4/0 Flex, 1/2" Stud, Short Barrel, Tin Plated

Product Details

General

Connector Type	Terminal
Die Index	46
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810025802

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.88 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - G inch	1.54 in
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	44 mm
Dimension - Length Overall inch	1.75 in
Dimension - N inch	0.48 in
Dimension - Outside Diameter inch	0.78 in
Dimension - Pad Width inch	1.12 in
Dimension - Stud Size inch	1/2 in
Dimension - Z inch	0.47 in
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper Str Aircraft Size	AN-4/0
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)