

YAV5002M12

by Burndy
Catalog ID: YAV5002M12

Non insulated Cu tubular terminals, 2 Hole/W/insp W, 500 mm Class2,
13.55 mm stud, Tin - Electro Plated, L115 Index



Product Details

General

Die Index	L115
Material	Copper
Plated	yes
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Metric Terminals
UPC	781810636459
UPC 12 Digit	7818106364599

Dimensions

Dimension - B Length inch	5.49 in
Dimension - Hole Size mm	13.5 mm
Dimension - L Length Overall mm	139.4 mm
Dimension - Length Overall inch	5.49 in
Dimension - Pad Width inch	55.6 in
Dimension - Strip Length inch	1.69 in
Dimension - Z inch	0.55 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	1000
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)