

YAZV262TC12E1FX

by Burndy
Catalog ID: YAZV262TC12E1FX

Prop 65 Notice

2 Hole HYLUG Cu Compr Terminal, Long Brrl, W/ Insp Window, 2/0 (325/#24) DLO, 2/0 AWG, 1/2" stud, 1" spacing, Black, 13 Index



Product Details

General

Color Code	Black
Connector Type	Terminal
Die Index	13
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Long Barrel, Skive
UPC	781810228470
UPC 12 Digit	7818102284700

Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.50 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4.01 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	0.63 in
Dimension - Pad Width inch	0.93 in
Dimension - Strip Length inch	1-9/16
Dimension - Z inch	0.56 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	2/0 (375/#24) DLO
Conductor - Copper DLO Size Range	2/0 (375/#24) DLO
Conductor - Copper Flex G Size	2/0 AWG
Conductor - Copper Flex G Size Range	2/0 AWG
Conductor - Copper Flex H Size	2/0 AWG
Conductor - Copper Flex H Size Range	2/0 AWG
Conductor - Copper Flex I Size	2/0 AWG
Conductor - Copper Flex I Size Range	2/0 AWG
Conductor - Copper Flex K Size	2/0 AWG
Conductor - Copper Flex K Size Range	2/0 AWG
Conductor - Copper Flex M Size	2/0 AWG
Conductor - Copper Flex M Size Range	2/0 AWG
Conductor - Copper Str Size	2/0 AWG
Conductor - CopperWeld Str Size	2/0 F AWG;2/0 G AWG;2/0 J AWG;2/0 K AWG;2/0 V AWG
Conductor - CopperWeld Str Size Range	2/0 F AWG-2/0 V AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	15
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)