



YBM25L1

by Burndy
Catalog ID: YBM25L1

Prop 65 Notice

Extruded Cu Flag Type Terminal, Ring Tongue, 1/0 Flex, 1/4" Stud, 1.49" L, 0.72" W, Tin plated, 58 Index.

Features: Made Of Pure Electrolytic Copper For Maximum Conductivity And Ductility, Seamless Extrusion Tin Plated To Resist Corrosion, Finish: Tin Plated, Wire Strip Length: 3/4 IN, Tools, Die Nest Catalog Number, Die Indentor Catalog Number: HYPRESS: Y29NC, Y29B, Y35, Y750 Tool, DV25BL-1 Die Nest, Y29PR Die Indentor, Installation Tool: HYTOOL: MY28 Tool

Product Details

General

Application	For use on copper compression connections
Connector Type	Terminal - Ring
Die Index	58
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	YBM
UPC	781810026311

Dimensions

Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.66 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Length Overall inch	1.49 in
Dimension - N inch	0.3 in
Dimension - Outside Diameter inch	0.67 in
Dimension - Pad Width inch	0.72 in
Dimension - Strip Length inch	5/8
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper DLO Size	1/0 (275/#24)
Conductor - Copper Flex I Size	1/0
Conductor - Copper Str Aircraft Size	AN 1/0
Conductor - Copper Str Size	1/0
Conductor - Copper Str Size Range	1/0
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)