

# YCAK30R4N

by Burndy  
Catalog ID: YCAK30R4N

Prop 65 Notice

Aluminium Terminal, 4 Pad Holes, 266.8 (18-1, 6-7, 26-7) kcmil ACSR, 266.8 (7, 19) kcmil Al., 251 Index



## Product Details

### General

Die Index	251
Material	Aluminum
Physical Attribute - Pad Configuration	4 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810016732
UPC 12 Digit	7818100167322

### Dimensions

Dimension - B Length inch	2.65 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	187 mm
Dimension - Length Overall inch	7.38 in
Dimension - Pad Width inch	3 in

### Conductor Related

Conductor - ACSR Str Size	266.8 (18-1) kcmil;266.8 (6-7) kcmil;266.8 (26-7) kcmil
Conductor - ACSR Str Size Range	266.8 (18-1) kcmil;266.8 (6-7) kcmil;266.8 (26-7) kcmil
Conductor - AL Str Size	266.8 kcmil
Conductor - AL Str Size Range	266.8 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity

1

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)