



## YCAK32R2G1

by Burndy  
Catalog ID: YCAK32R2G1

Prop 65 Notice

Cast Aluminum Compression Terminal, 2 Pad Holes, 3/0 AWG (7,19) Cu & Al, 350 (19,37) & 397.5 (19) kcmil, 336.4 (18 - 1, 26 - 7), 317 or 705 Index

## Product Details

### General

Die Index	317;705
Material	Aluminum, Cast
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810016619
UPC 12 Digit	7818100166199

### Dimensions

Dimension - B Length inch	3 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	184 mm
Dimension - Length Overall inch	7.25 in

### Conductor Related

Conductor - ACSR Str Size	336.4 kcmil
Conductor - AL Str Size	350 kcmil;397.5 kcmil
Conductor - AL Str Size Range	350 kcmil;397.5 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)