

YCR2C4W

by Burndy
Catalog ID: YCR2C4W

Prop 65 Notice

Cu Jumper Loop Sleeve Reducer, #2 - 7 Str Cu(Side A), #4 Sol (Side AA)



Product Details

General

Connector Type	Splice
Die Index	163
Material	Copper
Oxide Inhibitor Type	Penetrox A4
Plated	Y
Plating Type	Tin - Hot Dipped
Prefilled Oxide Inhibitor	Y
Trade Name	HYREDUCER™
UPC	781810014295

Dimensions

Dimension - A Outside Diameter inch	0.38 in
Dimension - B Length fraction	1-4/25 in
Dimension - B Length inch	1.16 in
Dimension - B Outside Diameter inch	0.5 in
Dimension - L Length Overall mm	95 mm
Dimension - Length BB inch	1.1 in
Dimension - Length Overall inch	3.73 in

Conductor Related

Conductor - Copper Solid Size B	4 AWG
Conductor - Copper Str Size A	2 AWG
Conductor - Copper Str Size A Range	2 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)