

YDS331AT

by Burndy
Catalog ID: YDS331AT

Prop 65 Notice

Aluminium Hysplice, 12-3/4 in L, Full Tension Sleeve for All Aluminum Compressed and Compact Conductors.

Features: Full-Tension HYSPLICE Sleeve Made Of Aluminum Tubing With Staked-In Cable Stop, Sizes 1/0 And Larger Tapered For Gradual Transition Of Stress, Installed With HYSPLICE Tools And Dies, Pre-Filled With PENETROX Joint Compound And Capped, Die Index: 317 Element A, Conductor Type: Aluminum, Compressed Aluminum, Compact Aluminum, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U317 Die, (9), Y45 Tool, U Die With Adapter PT-6515, Y46 Tool, U Die With Adapter PUADP-1



Product Details

General

| | |
|---------------------------|----------------------------------------------------|
| Application | For All Aluminum Compressed And Compact Conductors |
| Connector Type | Splice |
| Die Index | 317 |
| Insulation | Y |
| Material | Aluminum |
| Plated | N |
| Plating Type | Unplated |
| Prefilled Oxide Inhibitor | Y |
| Sub Brand | HYSPLICE |
| Trade Name | HYSPLICE™ |
| Type | YDS-AT |
| UPC | 781810821152 |
| UPC 12 Digit | 7818108211522 |

Dimensions

| | |
|-----------------------------------|-----------|
| Dimension - B Length fraction | 6-3/10 in |
| Dimension - B Length inch | 6.3 in |
| Dimension - L Length Overall mm | 323 mm |
| Dimension - Length Overall inch | 12.73 in |
| Dimension - Outside Diameter inch | 1.3 in |

Conductor Related

| | |
|---------------------------------|----------------------------------------------------------------------------------------------|
| Conductor - ACSR Str Size | 477.0 (18/1) Pelican kcmil |
| Conductor - ACSR Str Size Range | 477.0 (18/1) Pelican kcmil |
| Conductor - AL Str Size | 477 kcmil |
| Conductor - AL Str Size Range | 477 kcmil |
| Conductor Type | <ul style="list-style-type: none"> • ACSR C Str-Size • AL C Str-Size |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)