

# YDS3K10

by Burndy  
Catalog ID: YDS3K10

Prop 65 Notice

Full tension copper splice designed to exceed the rated breaking strength of 30 percentage high conductivity EHS copperweld and lower strength conductors, Die Index: 403.

Features: Full-Tension HYSPLICE Designed To Exceed The Minimum Rated Breaking Strength Of, 30 PCT Conductivity Extra High Strength Copperweld, And Lower Strength Conductors, Made Of Pure Copper Tubing, Installed With HYSPLICE Tools And Dies, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U403 Die, (3), Y45 Tool, U403 Die With PT-6515 Adapter, (3), Y46 Tool, U403 Die With PUADP-1 Adapter, (3), Die Index: 403 Element A, Conductor Type: Copperweld



## Product Details

### General

Application	For Copperweld Conductors
Connector Type	Splice
Die Index	403
Material	Copper
Physical Attribute - Number of Crimps Required	6
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
Sub Brand	HYSPLICE
Trade Name	HYSPLICE™
Type	YDS-K
UPC	781810014554

### Dimensions

Dimension - B Length fraction	20-1/2 in
Dimension - B Length inch	20.5 in
Dimension - L Length Overall mm	115 mm
Dimension - Length Overall inch	4.52 in
Dimension - Outside Diameter inch	0.53 in

### Conductor Related

Conductor - CopperWeld C Solid Size	4 AWG
Conductor - CopperWeld Str Size	3#10

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	50
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)