

# YDS500H

by Burndy  
Catalog ID: YDS500H

Prop 65 Notice

Full-tension steel splice designed for galvanized steel guy, messenger and "static:" conductors. ANSI C119.4 Class 1 (Full Tension), Die index: 293



## Product Details

### General

Connector Type	Splice
Die Index	293
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810016039

### Dimensions

Dimension - B Length fraction	4-22/31 in
Dimension - B Length inch	4.71 in
Dimension - L Length Overall mm	246 mm
Dimension - Length Overall inch	9.69 in
Dimension - Outside Diameter inch	0.97 in

### Conductor Related

Conductor - AL Coated Steel Size	1/2 (7) in
Conductor - AL Coated Steel Size Range	1/2 (7) in
Conductor - Galvanized Steel Str Size	1/2 (19) in
Conductor - Galvanized Steel Str Size Range	1/2 (19) in
Conductor - Grade	HS
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Size</li> <li>• AL C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed
-----------

No
----

## Logistics

Minimum Pack Quantity
-----------------------

1
---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)