

# YDS6WA

by Burndy  
Catalog ID: YDS6WA

Full tension aluminum splice with staked in cable stop. ANSI C199.4 Class 1 (Full Tension)



## Product Details

### General

Connector Type	Splice
Die Index	161
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810015414

### Dimensions

Dimension - B Length fraction	1-2/5 in
Dimension - B Length inch	1.4 in
Dimension - Inside Diameter inch	0.18 in
Dimension - L Length Overall mm	74 mm
Dimension - Length Overall inch	2.91 in
Dimension - Outside Diameter inch	0.33 in

### Conductor Related

Conductor - ACSR Cmpt Size	6 AWG
Conductor - ACSR Cmpt Size Range	6 AWG
Conductor - AL Str Size	6 AWG
Conductor - AL Str Size Range	6 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Size</li> <li>• AL C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)