

YDS7M6T

by Burndy
Catalog ID: YDS7M6T

Prop 65 Notice

Full Tension Sleeve for Alumoweld, 7 #6 AWG, 679 or 726 Index



Product Details

General

Connector Type	Splice
Die Index	679;726
Material	Aluminum
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYSPLICE™
UPC	781810015476

Dimensions

Dimension - B Length fraction	7-13/25 in
Dimension - B Length inch	7.52 in
Dimension - L Length Overall mm	385 mm
Dimension - Length Overall inch	15.17 in
Dimension - Outside Diameter inch	1.07 in

Conductor Related

Conductor - AWAC Size	1;1/0;2/0
Conductor - Alumoweld Size	7#6
Conductor Type	AWAC

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)