



YNA56RT

by Burndy
Catalog ID: YNA56RT

Prop 65 Notice

Compression Terminal , 1510-1590 kcmil ACSR 1700-1800 kcmil ALUM.
1650 kcmil ACAR 42-19 STR, 4 Pad holes, 12-3/4 in Length.

Features:Compression Terminal for ACSR Conductor

Product Details

General

Application	For use on: ACSR, ACAR and SAC Transmission Lines
Connector Type	Terminal
Die Index	729
Material	Aluminum
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	YNA-RT EHV
UPC	781810016411
UPC 12 Digit	7818100164111

Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	350 mm
Dimension - Length Overall inch	13.76 in
Dimension - Outside Diameter inch	2.5 in
Dimension - Pad Width inch	3.44 in
Dimension - Width fraction	3.44 in

Conductor Related

Conductor - ACAR Str Size	1650 KCMIL (42/19 STR)
Conductor - ACAR Str Size Range	1650 KCMIL (42/19 STR)
Conductor - ACSR Str Size	1510.5 (45/7) Nuthatch kcmil - 1590 (54/19) Falcon kcmil
Conductor - ACSR Str Size Range	1510.5 (45/7) Nuthatch kcmil - 1590 (54/19) Falcon kcmil
Conductor - AL Str Size	1700 KCMIL -1800 KCMIL
Conductor - AL Str Size Range	1700 KCMIL -1800 KCMIL

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)