



# YNA594RT

by Burndy  
Catalog ID: YNA594RT

Prop 65 Notice

HYLUG™, Al Tube Compression Terminal, 4 Holes, 2300 Kcmil ACSR, 2500 Kcmil Al, 2267-2500 Kcmil ACAR, 1.75" Spacing

## Product Details

### General

Connector Type	Terminal
Die Index	740
Material	Aluminum
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Orientation	Straight
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810016176
UPC 12 Digit	7818100161766

### Dimensions

Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	357 mm
Dimension - Length Overall inch	14.06 in
Dimension - Outside Diameter inch	2.6 in
Dimension - Pad Width inch	3.7 in
Dimension - Width fraction	3.70 in

### Conductor Related

Conductor - ACAR Str Size	2267 KCML - 2500 KCMIL
Conductor - ACAR Str Size Range	2267 KCML - 2500 KCMIL
Conductor - ACSR Str Size	2300 KCMIL
Conductor - ACSR Str Size Range	2300 KCMIL
Conductor - AL Str Size	2500 KCMIL
Conductor - AL Str Size Range	2500 KCMIL

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)