



## YNTA43R

by Burndy  
Catalog ID: YNTA43R

Prop 65 Notice

T-TAP WITH PAD TAP.

## Product Details

### General

Connector Type	Tap
Die Index	724
Material	Aluminum
Physical Attribute - Number of Holes	4
Physical Attribute - Pad Configuration	4 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	N
UPC	781810016565
UPC 12 Digit	7818100165655

### Dimensions

Dimension - B Length inch	4.53 in
Dimension - D inch	3.12
Dimension - F Width Center to Center inch	1.75
Dimension - Height fraction	5-9/25 in
Dimension - Height inch	5.36 in
Dimension - Hole Size inch	0.56
Dimension - Length Overall inch	17.48 in
Dimension - Outside Diameter inch	1.61 in
Dimension - Pad Width inch	3.25 in

### Conductor Related

Conductor - ACSR Str Size	605 (24/7) kcmil;605 (26/7) kcmil;636 (24/7) kcmil;636 (26/7) kcmil;666.6 (24/7) kcmil
Conductor - ACSR Str Size Range	605 (24/7) kcmil-666.6 (24/7) kcmil
Conductor - AL Str Size	700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil
Conductor - AL Str Size Range	700 kcmil-800 kcmil

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)