

YPC36A36

by Burndy
Catalog ID: YPC36A36

Figure 6 shape connector separates run and tap wires and minimizes galvanic corrosion of conductors, Run, Al and Cu:397.5 (19) - 600 (61)



Product Details

General

Die Index	Z
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	CRIMPIT™
UPC	781810138601
UPC 12 Digit	7818101386011

Dimensions

Dimension - Height inch	3.70 in
Dimension - L Length Overall mm	171 mm
Dimension - Length Overall inch	6.75 in
Dimension - Width inch	1.88 in

Conductor Related

Conductor - ACSR Str Run Range	336.4 kcmil-556.5 kcmil
Conductor - ACSR Str Tap Range	336.4 kcmil-556.5 kcmil
Conductor - AL Str Run	397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil
Conductor - AL Str Run Range	397 kcmil-600 kcmil
Conductor - AL Str Tap	397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil
Conductor - AL Str Tap Range	397 kcmil-600 kcmil
Conductor - Copper Str Run	397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil
Conductor - Copper Str Run Range	397 kcmil-600 kcmil
Conductor - Copper Str Tap	397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil
Conductor - Copper Str Tap Range	397 kcmil-600 kcmil

Conductor Type	<ul style="list-style-type: none"> • AL C Str-Run • CU C Str-Run • CU C Solid-Run • ACSR C Str-Run • AL C Str-Tap • CU C Str-Tap • CU C Solid-Tap • ACSR C Str-Tap
----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)