



## YS26AG4

by Burndy  
Catalog ID: YS26AG4

Prop 65 Notice

Al Service Repair Splice, 2/0 Str Al & Cu, 10.00" L

### Product Details

#### General

Connector Type	Splice
Die Index	K-840
Feature - Barrel Style	Tapered
Insulation	Y
Insulation Type	Rubber
Material	Aluminum
Physical Attribute - Number of Crimps Required	2
Plated	N
Plating Type	Unplated
UPC	781810001455

#### Dimensions

Dimension - L Length Overall mm	254 mm
Dimension - Length Overall inch	10 in
Dimension - Outside Diameter inch	0.91 in
Dimension - Strip Length inch	2

#### Conductor Related

Conductor - AL Str Size	2/0 AWG
Conductor - Copper Str Size	2/0 AWG

#### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

#### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)