

YS28PULL

by Burndy
Catalog ID: YS28PULL

Hylink Cu compression long barrel code splice tubing, Beveled entry, 4/0 STR kcmil.Cu, 600V-35KV, Tin plated, Purple, 15 Index.

Features: Long barrel length, Four center conductor stops, High pull out force



Product Details

General

Application	For heavy duty applications
Color Code	Purple
Connector Type	Splice
Die Index	15
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Bright
Sub Brand	SPLICE, HYLINK
Trade Name	HYLINK™
Type	Type YS
UPC	781810105115
UPC 12 Digit	7818101051155

Dimensions

Dimension - B Length inch	1.58 in
Dimension - L Length Overall mm	90 mm
Dimension - Length Overall inch	3.56 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	4/0 AWG
-----------------------------	---------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)