



YS2CAT

by Burndy
Catalog ID: YS2CAT

Prop 65 Notice

Al Comp Splice,High Voltage Uninsul, Tapered Ends, #2 Str(Al), 35 KV,
4.00" L, 348 Index

Product Details

General

Color Code	Pink
Connector Type	Splice
Die Index	348
Feature - Barrel Style	Tapered
Feature - Barrel Type	Standard
Material	Aluminum
Physical Attribute - Number of Crimps Required	2
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLINK™
UPC	781810001356

Dimensions

Dimension - B Length inch	1.58 in
Dimension - L Length Overall mm	102 mm
Dimension - Length Overall inch	4.00 in
Dimension - Outside Diameter inch	0.53 in
Dimension - Pad Width inch	1.93 in
Dimension - Strip Length inch	2 1/4

Conductor Related

Conductor - AL Str Size	2 AWG
-------------------------	-------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)