

YS32PULL

by Burndy
Catalog ID: YS32PULL

HYLINK™ Cu compression long barrel code splice tubing, Beveled entry,
400 kcmil.Cu, 600V-35KV, Tin plated, Blue, 19 or 470 Index



Product Details

General

Color Code	Blue
Connector Type	Splice
Die Index	19;470
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Bright
Trade Name	HYLINK™
UPC	781810091920
UPC 12 Digit	7818100919200

Dimensions

Dimension - B Length inch	2.08 in
Dimension - L Length Overall mm	117 mm
Dimension - Length Overall inch	4.61 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	400 kcmil
-----------------------------	-----------

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)