

## YS3CPULL

by Burndy  
Catalog ID: YS3CPULL

HYLINK™ Cu compression long barrel code splice tubing, Beveled entry, 3 AWG.CU, 600V-35KV, Tin plated, White, 9 index



## Product Details

### General

Color Code	White
Connector Type	Splice
Die Index	9
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Bright
Trade Name	HYLINK™
UPC	781810055717
UPC 12 Digit	7818100557177

### Dimensions

Dimension - B Length inch	1.22 in
Dimension - L Length Overall mm	71 mm
Dimension - Length Overall inch	2.80 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Size	3 AWG
-----------------------------	-------

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)