

YS4CPULL

by Burndy
Catalog ID: YS4CPULL

Cu compression splice, #4 splice, Grey, 8 or 346 index.

Long barrel length, Four center conductor stops, High pull out force



Product Details

General

Application	For heavy duty applications
Color Code	Gray
Connector Type	Splice
Die Index	8;346
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Bright
Sub Brand	HYLINK,SPLICE
Trade Name	HYLINK™
Type	YS
UPC	781810096840
UPC 12 Digit	7818100968400

Dimensions

Dimension - B Length inch	1.10 in
Dimension - L Length Overall mm	65 mm
Dimension - Length Overall inch	2.55 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	4 AWG
-----------------------------	-------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)