

YS8CPULL

by Burndy
Catalog ID: YS8CPULL

HYLINK™ Cu compressiion long barrel code splice tubing, Beveled entry, 8 AWG.CU, 600V-35KV, Tin plated, Red, 49 index



Product Details

General

Color Code	Red
Connector Type	Splice
Die Index	49
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Bright
Trade Name	HYLINK™
UPC	781810059548
UPC 12 Digit	7818100595488

Dimensions

Dimension - B Length inch	0.78 in
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.93 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Size	8 AWG
-----------------------------	-------

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	50
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)